

Sartoclear Dynamics[®] Lab For Convenient Mammalian Cell Culture Harvesting





Sartoclear Dynamics® Lab

70% Faster Clarification and Sterile Filtration of up to 1,000 mL Mammalian Cell Cultures


Sartoclear Dynamics[®] Lab is a new, one-step method for harvesting mammalian cell cultures with high cell densities. Consistent results, ease of use and exceptional speed are the key characteristics of this technology.

Inspired by the plasma industry, Sartoclear Dynamics® Lab is based on the principles of body feed filtration. The ready-to-use clarification kits enable convenient and fast processing of up to 1,000 mL. As a result, these one-step kits eliminate the lengthy centrifugation step.

Your Current Clarification Challenge

In the past decade, the productivity of fed-batch mammalian cell cultures has risen significantly. Driven by optimized strains and culture media, titers have increased from 1-3~g/L to 7-10~g/L.

Today, the common procedure of cell removal is to centrifuge broth to partly remove cells and cell debris first, then to pass the sample through a sterile filter unit. High cell density prolongs the time required for centrifugation. Even after centrifugation, subsequent sterile filtration normally cannot be performed using just one filter as it rapidly becomes clogged.



With Sartoclear Dynamics® Lab kits, you can now clarify and sterile-filter your mammalian cell culture of up to 1,000 mL quickly and easily in a single step.

Sartoclear Dynamics[®] Lab P15 Cell Harvesting of up to 15 mL Mammalian Cell Cultures in One Step

This ready-to-use kit combines a 20 mL syringe pre-filled with 0.5 g of filter aid for clarification and a syringe filter for sterile filtration. The filter aid facilitates filtration through the sterile filter while allowing complete protein recovery.

Clarification

A 20 mL syringe pre-filled with 0.5 g filter aid for clarification of cell culture samples of any cell density. The filter aid is made of highly pure diatomaceous earth (DE), an optimized grade for cell culture harvests, which is inert and insoluble.



Sterile Filtration

The sterile filter is a 0.2 µm polyethersulfone membrane and the prefilter is made of 100% high-purity quartz: The choice of these materials, along with the large surface area of the filters, enables high flow rates.

broth.



1. Fill the syringe with cell culture

Clarification and sterile filtration of mammalian cell

cultures are performed in a single pressure filtration step.

3. Connect the sterile filter to the syringe and filter.



2. Shake the syringe to mix the broth with the filter aid.



4. One minute later, the clarified cell culture liquid is available for subsequent downstream processing steps, such as protein purification and concentration.



A convenient filling tube for easy recovery of samples from 50 mL Falcon tubes or ambr[®] 15 bioreactors.

Sartoclear Dynamics® Lab V Cell Harvesting of 50 mL to 1,000 mL Mammalian Cell Cultures in One Step

The ready-to-use Sartoclear Dynamics Lab V kits combine pouches of filter aid for clarification and vacuum filtration units for sterile filtration. The filter aid facilitates filtration through the sterile filter while allowing complete protein recovery.



Clarification

Pouches filled with pre-wetted, highly pure diatomaceous earth (DE) for dust-free transfer

- Optimized grade for cell culture harvests
- Inert and insoluble
- Sizes: Pouches with 1 g, 5 g and 10 g of sterile and endotoxin-free DE

Sterile Filtration

Sterile vacuum filtration units in capacities ranging from 50 mL to 1,000 mL including conical tube for the 50 mL version and receiver flasks for the larger versions

- 0.22 μm polyethersulfone membrane
- The fastest flow rates
- Low protein binding and low extractables



Clarification and sterile filtration are performed in a single step, which enables cell cultures to be efficiently clarified and sterilized in minutes.



1. Attach the Sartolab® RF unit to a vacuum source. Pour the filter aid into your cell culture.



Sartolab

180C2 0.22 μm PES

the Sartolab® RF first, ...



3. ... then filter by simply using the



4. After 5 – 15 min., the sample will be available for subsequent downstream processing steps, such as protein purification and concentration.

Sartolab® MultiStation for Hands-Free Parallel Filtration of up to Six Samples



Hands-free parallel clarification and sterile filtration of cell cultures in just a few seconds



1. Attach the Sartolab® RF 50 unit to the MultiStation on hold position (first click).



2. Pour the cell culture and filter aid mixture into the Sartolab® RF 50.




3. Push the filtration unit to apply vacuum to the unit and to start the filtration (second click).



4. Rotate the head of the MultiStation and filter the next samples or remove the filtration unit after filtration.

The Reality Check— Example of a 1,000 mL Cell Culture

- 1,000 mL
- Chinese Hamster Ovary (CHO) line
- 11 million cells/mL
- 75% viability



Ordering Information

1 Kit for Filtration of 15 mL Cell Cultures of Any Density

Description	Qty. of Units	Order No.
Sartoclear Dynamics® Lab P15		
6 x 20 mL syringes, pre-filled with 0.5 g of DE, including caps and filling tubes, 6 x sterile filters	6	SDLP0015C

2 Kits for Filtration of 15 to 50 mL Cell Cultures

Description	Qty. of Units	Order No.
Filtration of 15 mL to 50 mL mammalian cell cultures		
Sartoclear Dynamics® Lab V, 50 mL, 1 g		
Filtration of 15 mL to 50 mL with 1 g of DE per unit Contents: 1 x 180E012 (24 x Sartolab® RF 50; 0.22 μm; PES; single-packaged; sterile) 1 x SDLKG-01.02 (24 x pouches of filter aid, 1 g)	24	SDLV-0050-01E0-2
Sartoclear Dynamics® Lab V, 50 mL, 2 g		
Filtration of 15 mL to 50 mL with 2 g of DE per unit Contents: 1 x 180E012 (24 x Sartolab® RF 50; 0.22 μm; PES; single-packaged; sterile) 2 x SDLKG-01.02 (48 x pouches of filter aid. 1 g)	24	SDLV-0050-02E0-2

Sartolab® MultiStation

Description	Qty. of Units	Order No.
Filtration of 15 mL to 50 mL mammalian cell cultures		
Sartolab [®] MultiStation		
For hands-free parallel filtration of up to six samples	1	SDLC01

Ordering Information continues on next page



Ordering Information (Continued from preceding page)

10 Kits for Filtration of > 50 mL to 1,000 mL Cell Cultures

Description	Qty. of Units	Order No.
Filtration of > 50 mL to 150 mL mammalian cell cultures		
Sartoclear Dynamics [®] Lab V, 150 mL, 2 g		
Filtration of > 50 mL to 150 mL with 2 g of DE per unit	12	SDLV-0150-02CE
Contents: 1 x 180C1E (12 x Sartolab® RF 150; 0.22 µm; PES; single-packaged; sterile)		
1 x SDLKG-01.02 (24 x pouches of filter aid, 1 g)		
Sartoclear Dynamics® Lab V, 150 mL, 5 g		
Filtration of > 50 mL to 150 mL with 5 g of DE per unit	24	SDLV-0150-05C2
Contents: 2 x 180C1E (24 x Sartolab® RF 150; 0.22 μm; PES; single-packaged; sterile)		
1 x SDLKG-05.02 (24 x pouches of filter aid, 5 g)		
Filtration of 125 mL to 250 mL mammalian cell cultures		
Sartoclear Dynamics® Lab V, 250 mL, 5 g		
Filtration of up to 250 mL with 5 g of DE per unit	24	SDLV-0250-05C2
Contents: 2 x 180C7 (24 x Sartolab® RF 250; 0.22 µm; PES, single-packaged; sterile)		
1 x SDLKG-05.02 (24 x pouches of filter aid, 5 g)		
Sartoclear Dynamics® Lab V, 250 mL, 10 g		
Filtration of up to 250 mL with 10 q of DE per unit	24	SDLV-0250-10C2
Contents: 2 x 180C7 E (24 x Sartolab® RF 250; 0.22 µm; PES; single-packaged; sterile)		
1 x SDLKG-10.02 (24 x pouches of filter aid, 10 g)		

Description	Qty. of Units	Order No.
Filtration of 250 mL to 500 mL mammalian cell cultures		
Sartoclear Dynamics® Lab V, 500 mL, 5 g		
Filtration of up to 500 mL with 5 g of DE per unit Contents: 2 x 180C2E (24 x Sartolab® RF 500; 0.22 µm; PES; single-packaged; sterile) 1 x SDLKG-05.02 (24 x pouches of filter aid, 5 g)	24	SDLV-0500-05C2
Sartoclear Dynamics® Lab V, 500 mL, 10 g		
Filtration of up to 500 mL with 10 g of DE per unit Contents: 2 x 180C2 (24 x Sartolab® RF 500; 0.22 µm; PES, single-packaged; sterile) 1 x SDLKG-10.02 (24 x pouches of filter aid, 10 g)	24	SDLV-0500-10C2
Sartoclear Dynamics® Lab V, 500 mL, 20 g		
Filtration of up to 500 mL with 20 g of DE per unit Contents: 1 x 180C2 E (12 x Sartolab® RF 500; 0.22 µm; PES; single-packaged; sterile) 1 x SDLKG-10.02 (24 x pouches of filter aid, 10 g)	12	SDLV-0500-20CE
Filtration of 500 mL to 1,000 mL mammalian cell cultures		
Sartoclear Dynamics Lab V, 1,000 mL, 10 g Filtration of up to 1,000 mL with 10 g of DE per unit Contents: 2 x 180C3 [24 x Sartolab RF 1000; 0.22 µm: PES; single-packaged; sterile) 1 x SDLKG-10.0 2 (24 x pouches of filter aid, 10 g)	24	SDLV-1000-10C2
1 x 3DLKG-10.02 (24 x pouches of filter ald, 10 g)		
Sartoclear Dynamics Lab V, 1,000 mL, 20 g		
	12	SDLV-1000-20CE
Sartoclear Dynamics Lab V, 1,000 mL, 20 g Filtration of up to 1,000 mL with 20 g of DE per unit Contents: 1 x 180C3E (12 x Sartolab RF 1000; 0.22 µm; PES; single-packaged; sterile)	12	SDLV-1000-20CE

Sales and Service Contacts

For further contacts, visit www.sartorius.com

Europe

Germany

Sartorius Lab Instruments GmbH & Co. KG Otto-Brenner-Strasse 20 37079 Goettingen

Phone +49.551.308.0

France & Suisse Romande

Sartorius France 2, rue Antoine Laurent de Lavoisier ZA de la Gaudrée 91410 Dourdan

Phone +33.1.70.62.50.00

Sartorius Austria GmbH Modecenterstrasse 22 1030 Vienna

Phone +43.1.7965760.0

Belgium

Sartorius Belgium N.V. Rue Colonel Bourg 105 1030 Bruxelles

Phone +32.2.756.06.90

Finland & Baltics

Sartorius Biohit Liquid Handling Oy Laippatie 1 00880 Helsinki

Phone +358.9.755.951

Hungary

Sartorius Hungária Kft. Kagyló u. 5. 2092 Budakeszi

Phone +3623.457.227

Sartorius Ireland Ltd. Unit 41, The Business Centre Stadium Business Park Ballycoolin Road

Phone +353.1.8089050

Italy

Sartorius Italy S.r.l. Via Torino 3/5 20814 Varedo (MB)

Phone +39.0362.5557.11

Netherlands

Sartorius Netherlands B.V.

Phone +31.30.60.53.001

info.netherlands@sartorius.com

Sartorius Poland sp.z o.o. ul. Wrzesinska 70 62-025 Kostrzyn

Phone +48.61.6473830

Russian Federation LLC "Sartorius RUS" Vasilyevsky Island 5th line 70, Lit. A 199178 St. Petersburg

Phone +7.812.327.53.27

Spain & Portugal

Sartorius Spain, S.A. Avda. de la Industria, 32 Edificio PAYMA 28108 Alcobendas (Madrid)

Phone Spain +34.913.586.095 Phone Portugal +351.800.855.800

Switzerland

Sartorius Mechatronics Switzerland AG Ringstrasse 24a 8317 Tagelswangen (ZH)

Phone +41.44.746.50.00

Sartorius UK Ltd. Longmead Business Centre Blenheim Road, Epsom Surrey KT19 9QQ

Phone +44.1372.737159

LLS "Sartorius RUS" Post Box 440 "B" 01001 Kiev, Ukraine

Phone +380.44.411.4918

Americas

USA

Sartorius Corporation 5 Orville Drive, Suite 200 Bohemia, NY 11716

Phone +1.631.254.4249 Toll-free +1.800.635.2906

Argentina

Sartorius Argentina S.A. Int. A. Ávalos 4251 B1605ECS Munro **Buenos Aires**

Phone +54.11.4721.0505

Sartorius do Brasil Ltda Avenida Senador Vergueiro 2962 São Bernardo do Campo CEP 09600-000 - SP- Brasil

Phone +55.11.4362.8900

Canada

Sartorius Canada Inc 1173 North Service Road West, D4 Oakville, ON L6M 2V9

Phone +1.905.569.7977 Toll-Free +1.800.668.4234

Mexico

Sartorius de México, S.A. de C.V. Libramiento Norte de Tepotzotlan s/n, Colonia Barrio Tlacateco, Municipio de Tepotzotlan, Estado de México, C.P. 54605

Phone +52.55.5562.1102

leadsmex@sartorius.com

Sartorius Peru S.A.C. Avenue Alberto del Campo 411 Floor 12 - The Office 15076 - San Isidro, Lima

Phone +51.1.441 0158

Asia | Pacific

Australia

Sartorius Australia Pty. Ltd. Unit 5, 7-11 Rodeo Drive Dandenong South Vic 3175

Phone +61.3.8762.1800

Sartorius (Shanghai) Trading Co., Ltd. 3rd Floor, North Wing, Tower 1 No. 4560 Jinke Road Zhangjiang Hi-Tech Park **Pudong District** Shanghai 201210, P.R. China

Phone +86.21.6878.2300

Hong Kong

Sartorius Hong Kong Ltd. Unit 1012, Lu Plaza 2 Wing Yip Street Kwun Tong Kowloon, Hong Kong

Phone +852.2774.2678

India

Sartorius Weighing India Pvt. Ltd. #69/2-69/3, NH 48, Jakkasandra, Nelamangala Tq 562 123 Bangalore, India

Phone +91.80.4350.5250

Japan

Sartorius Japan K.K. 4th Fl., Daiwa Shinagawa North Bldg. 8-11, Kita-Shinagawa 1-chome Shinagawa-ku, Tokyo, 140-0001 Japan

Phone +81.3.3740.5408

Malaysia

Sartorius Malaysia Sdn. Bhd Lot L3-E-3B, Enterprise 4 Technology Park Malaysia Bukit Jalil 57000 Kuala Lumpur, Malaysia

Phone +60.3.8996.0622

Singapore

Sartorius Singapore Pte. Ltd 10 Science Park Rd The Alpha #02-13/14 Singapore Science Park II Singapore 117684

Phone +65.6872.3966

South Korea

Sartorius Korea Ltd. 8th Floor, Solid Space B/D, PanGyoYeok-Ro 220, BunDang-Gu SeongNam-Si, GyeongGi-Do, 463-400 Phone +82.31.622.5700

Thailand

Sartorius (Thailand) Co. Ltd. 129 Rama 9 Road, Huaykwang Bangkok 10310

Phone +66.2643.8361-6

Follow us







