Jumbo Star Sartopure® GA

The Giant-Sized Venting Cartridge



Benefits

- Air filter cartridge with extremely high throughput
- Highest filtration area on smallest footprint

Product Information

The Jumbo Star Sartopure® GA cartridge is designed for all venting applications that do not necessarily require an integrity testable membrane filter cartridge.

Application

Featuring a retention of 0.2 µm for gas, Jumbo Star Sartopure® GA efficiently protects stored products in the food and beverage industry. Ideally designed for special reservoirs and storage tanks with a high capacity.

Security

The Jumbo Star Sartopure® GA filter elements ensure selective and defined particle and bioburden retention.

Performance

Jumbo Star Sartopure® GA offers an optimized ratio of air flow rate and retention as well as outstanding hydrophobicity.

Flexibility

The modular concept allows the ideal adaptation to customer requirements. Jumbo Star Sartopure® GA filter cartridges are available in two different heights.

Documentation

Jumbo Star Sartopure® GA filter cartridges are designed, developed and manufactured in accordance with a ISO 9001 Quality Management System.

Technical Data

Specifications

| Materials | |
|-----------------|-------------------------------|
| Filter Material | Glass fibre and polypropylene |
| Support Fleece | Polypropylene |
| Core | Polypropylene |
| End Caps | Polypropylene |
| O-Rings | Silicone |

Retention Rates

0.2 µm

Available Sizes | Filtration Area

Size 1 10" 15 m² Size 2 20" 30 m²


Available Adapter

40

| Operating Parameters | | |
|---|--|--|
| Max. Allowable Differential Pressure | 4 bar 58 psi at 20°C 1 bar 15 psi at 80°C 0.5 bar 7.5 psi at 120°C | |
| Max. Allowable Back Pressure | 1.5 bar 22 psi at 20°C | |

| Sterilisation | | | | |
|------------------|---------|--------|--|--|
| Hot Water | 85-95°C | 30 min | | |
| In-line Steaming | 110°C | 30 min | | |

Air Flow Rates Jumbo Star Sartopure® GA (height 10")



Ordering Information

| Order Code | Size | Retention Rate |
|-------------|------|----------------|
| 5594007J1GA | 10" | 0.2 μm |
| 5594007J2GA | 20" | 0.2 um |

Germany

Sartorius Stedim Biotech GmbH August-Spindler-Strasse 11 37079 Goettingen Phone +49 551 308 0

USA

Sartorius Stedim North America Inc. 565 Johnson Avenue Bohemia, NY 11716 Toll-Free +1 800 368 7178

For further contacts, visit www.sartorius.com