

## **Product Datasheet**

# Masterflex<sup>®</sup> Easy-Load<sup>®</sup> Pump Heads

Reliable Fluid Transfer for Vivaflow® Cassettes



## Benefits

- Quick and simple tubing changes
- Adjustment-free automatic tubing retention
- Compatible with multiple tubing sizes
- Highly durable, low maintenance design

### Product Information

Masterflex® Easy-Load® pump heads perfectly complement Vivaflow® crossflow filtration cassettes, whilst also offering the flexibility, durability and performance needed in multiple other fluid-transfer applications.

Tubing changes are fast and easy, thanks to the single-thumb operated lever and automatic tubing retention. Two versions are offered, both compatible with multiple tubing sizes, extending their suitability to further applications, and the hard-wearing materials ensure long-term durability.

# Technical Specifications

Order Number	VFA012	VFA013  Easy-Load® pump head (size 15)	
Description	Easy-Load® pump head (size 16)		
Dimensions (L   W   H)	64   105   105 mm	64   105   105 mm	
Minimum flow rate	0.0012 mL/min	0.034 mL/min	
Maximum flow rate	2,300 mL/min	1,700 mL/min	
Housing material	Polyarylamide (PARA)	Polyarylamide (PARA)	
Rotor material	SS* with PTFE coated bearings	SS* with PTFE coated bearings	
Rollers	4x SS*	4x SS*	
Tubing sizes	13, 14, 16, 25, 17, 18	15, 24	
Optimum speed range	0.02 - 600 rpm	0.02 - 600 rpm	
Volume per revolution Size 16 tubing Size 15 tubing	0.8 mL -	- 1.7 mL	
Maximum vacuum, size 16 or 15 tubing	660 mm Hg	660 mm Hg	
Suction lift, size 16 or 15 tubing	8.8 m H <sub>2</sub> O	8.8 m H <sub>2</sub> O	
Maximum pressure, size 16 or 15 tubing	2.7 bar	2.7 bar	

<sup>\*</sup>SS= Stainless Steel

## Ordering Information

Description	Pack size	Order no.
Masterflex® Easy-Load® pump head (size 16)	1	VFA012
Masterflex® Easy-Load® pump head (size 15)	1	VFA013

## Addtional Equipment and Accessories

Description	Pack size	Order no.
Masterflex® variable-speed peristaltic pump (240 V)	1	VFP001
Masterflex® variable-speed peristaltic pump (115 V)	1	VFP002
Size 16 PVC pump tubing and luer fittings (3 m, 3.2 mm ID, 1.6 mm WT)	1	VFA004
Size 15 PVC pump tubing and luer fittings (3 m, 4.8 mm ID, 2.6 mm WT)	1	VFA003

#### Germany

Sartorius Lab Instruments GmbH & Co. KG Otto-Brenner-Strasse 20 37079 Goettingen Phone +49 551 308 0

For further contacts, visit www.sartorius.com

#### USA

Sartorius Corporation 565 Johnson Avenue Bohemia, NY 11716 Phone +1 631 254 4249 Toll-free +1 800 635 2906