SVISCISVS

Application Note

November 30, 2021

Keywords or phrases

Recombinat Protein, Proteins, Concentration, Diafiltration, Clarification, Hollow Fiber, Ultrafiltration, Single-use TFF

Recombinant Protein – Pilot Scale Concentration – 12.5 g/L

Bengt Persson*

Sartorius Stedim North America Inc., 565 Johnson Avenue, Bohemia, NY 11716, United States

* Correspondence Email: bengt.persson@sartorius.com

Abstract

This application note is focusing on the concentration and diafiltration of a 150 kD recombinant protein. With a target concentration of 12.5 g/L.

The goal was to determine the optimum operating conditions to maximize the retention of the protein at a favorable permeate flux rate. The Re-use line Investigator in 24-inch lengths and 30 kD MWCO with a 1.0 mm fiber ID was used for this trial. I was shown that no passage of the recombinant protein into the permeate happened, therefore 100% of the product were retained. The process target of \geq 10× concentration was even exceeded when the actual concentration was >15× with a processing time of 1.6 hours.

Charaction

In the following you will see application data from a concentration step of a recombinant protein production process. The goal was to determine an optimum membrane loading and permeate flux rate to maintain a stable and TMP \leq 5 psig while maximum transmission of 150 kD target protein.



Given the characteristics of the target protein (150kD) a Hollow Fiber Module with a MWCO of 30kD was chosen. The optimum operating conditions and maximum retention of the protein at a favorable permeate flux rate should be defined.

Feed:

- Recombinant Protein: 150 kD
- Concentration: 12.5 g/L

Details of Trial

| Membrane & Module | Re-use line Explorer 24-inch 30 kD, m-PES, 0.27 m², 1 mm fiber ID |
|-------------------|---|
| Process (target) | >10× concentration in approximately 2 hours |
| Process Condition | >14 LMH (4000 sec ⁻¹) |
| | |



For this concentration and diafiltration of a 150 kD recombinant protein a Re-use line Investigator was used. The length of 24-inch and a MWCO of 30 kD and 1.0 mm fiber ID where chosen. Like all our Hollow Fiber modules the membrane consisted of modified Polyethersulfone (m-PES). The Investigator module has a diameter of 3.3 cm and a corresponding filter area of 0.28 m².

Details of used Hollow Fiber Module

| Family | Re-use |
|---|----------------------------|
| Product Size | Investigator |
| MWCO Pore Size | 30 kD |
| Fiber ID | 1.0 mm |
| Length | 24 inch |
| Filter Area | 0.28 m ² |
| Crossflow rate ~ 4,000 sec ⁻¹ [L/h] | 240 |
| No. of Fibers | 160 |
| Recommended batch volume per module | 2 - 12 L |
| Diameter Module (cm) | 3.30 cm |
| Feed Retentate connectors | 1.5-inch TC |
| Permeate connector | ½-inch TC |
| Material | WA03010INV24S0 (1-pack) |



During optimization, the flux vs. TMP (Figure 1) shows that process conditions were optimum for this recombinant protein. Figure 2 for filtrate flux vs. concentration factor shows the process was able to exceed to process targets of $\geq 10 \times$ concentration of the recombinant protein within 2 hours.

Optimization: TMP vs. Flux Rate

Optimization: TMP vs. Flux Rate




Figure 1: Filtrate Flux rate vs. TMP for recombinant protein




Figure 1: Filtrate flux profile for concentration of recombinant protein from 12.5 g/L to 190 g/L (>15× concentration)

Conclusion

The average permeate flux rate was 12 LMH during the concentration process. Using the 30 kD membrane showed no passage of the recombinant protein into the permeate, therefore retaining 100% of the product. The process target of \geq 10x concentration was exceeded when the actual concentration was >15× with a processing time of 1.6 hours.

Germany

USA

Sartorius Stedim Biotech GmbH August-Spindler-Strasse 11 37079 Goettingen Phone +49 551 308 0 Sartorius Stedim North America Inc. 565 Johnson Avenue Bohemia, NY 11716 Toll-Free +1 800 368 7178

⊕ For more information, visit ■

www.sartorius.com